
Micro/Vickers CCD Image Automatic Measuring System

Standard Delivery

Computer (CPU: I3, Hard disk: 500G,	
• • •	
Memory: 4G, 19 inch LCD screen)	1
Ink Jet Printer	1
CCD Camera (1.30 Million Pixel)	1
Adapter Tube	1
USB Softdog	1
Measuring Software	1





Features

CCD Image automatic measuring system combines the computer software and the hardness tester, the whole test procedure is finished through the easy operation of keyboard and mouse click, which avoids the visual fatigue and man-made error and can test different kinds of hardness. It is equipped with a CCD camera easy to observe, and can directly observe and measure the indentation on the display. For test conditions of setting, the results can be clearly and conveniently operated and displayed. By measuring software, it can achieve a single point measurement and random multipoint measurement, data statistical measurement, arbitrary two-point or multipoint measurement for the spacing layer depth. It can be measured along the X or Y two direction, automatically carry out the calculation of infiltration depth, statistical calculations, conversion, display curve, judging whether qualified according to the input decision value (such as 550) and save the result as WORD or EXCEL documents.

The measurement and control of the tester system is to use high resolution image device, display the indentation clearly on the computer screen. Through the software for signal conversion, it automatically measures the hardness value of indentation. By designated and continuous testing process, it can draw the depth and gradient curve diagram. It supports WIN7, WINXP etc operating system. The Vickers, Knoop and carburizing layer can be tested. Hardness value can be carried out various forms of automatic conversion. You can choose high or low magnification objective lens according to your need. Image definition: > 540lines. It can regulate the contrast and brightness of the image, can respectively open, store or print the image files and data files. You can view the data files and image files any time, and print the data files by the form of tables and curves.

V3.0 Micro/Vicker Hardness Automatic Measuring System

Features

V3.0 Automatic Vickers Hardness Measuring System is integrated with several new technologies such as optical imaging, mechanical displacement, electronic control, digital imaging, image analysis, computer processing and so on. It controls the Vickers hardness tester and automatic test table by the computer, and displays the indentation image on the computer screen. By means of automatic reading and manual reading, it accurately measures the HV hardness, hardening depth, film thickness, distance between two points of metals and some non-metallic materials and various films. It also can shoot metal surface morphology and taking fixed rate printing etc. This system breaks through the traditional test method, realize the hardness test of fully automatic, high precision, high repeatability, and it is the important equipment for materials analysis.



Technical Specification

Computer	CPU: I5, 4G memory, 500G hard disk, 19 inch LCD screen
Operating system	WIN XP, WIN7
Digital imaging system	High resolution: 130 million pixel, 1280×1024 High speed acquisition: 1280×1024 resolution: 25 FPS High definition: Black and white images and clarity is better. Target surface size: 1/2 inch
X-Y automatic test table	Table size: 110×110×41 mm Maximum travel: 50×50 mm Minimum step: Less than 2µm Movement speed: Adjustable Control mode: Manual control, electric control, computer control
X-Y test table - computer control mode	Location movement: The test table directly moves to the software settings; Point movement: Select any point of the sample, moved to the below of the indenter; Directional movement: Click the eight directions to make the test table move and the moving step can be set up; Arbitrary movement: Click any directions to make the test table move and make it easy for users to browse the specimen surface; Variable speed movement: There are two speeds (fast and slow) when moving the test table and the speed is optional and adjustable; Other function: Original position arbitrary setting, automatic reset, mechanical limit, and other professional features to meet various requirements.
Measuring method	Automatic mode——Automatic test table moving (X, Y, Z direction) + automatic reading Manual mode 1——Automatic loading + manual eyepiece scribed line measurement Manual mode 2——Manual test table moving + manual focus + Automatic / manual measurement
Automatic / manual reading	Automatic reading time: Single indentation reading time is about 300 milliseconds; Automatic measurement precision: 0.1µm; Automatic measurement repeatability: ±0.8% Manual reading: Manual pick, automatic search points, 4 points measurement, 2 diagonal measurement
Results save / output	Save / output measurement data and experimental parameters, including D1, D2, HV, X, Y etc.; Save / output effective hardening layer depth curve report; Save / output image.

Software Functions

- •System linkage: Through the communication interface it realizes the linkage between the system and the hardness tester.
- Pressure linkage: When converting test force, the system percepts the test force change and displays in real time.
- •Turret linkage: The software controls the shifting between the objective and the indenter without manual control.
- •Loading linkage: The software controls the loading without manual control.
- •Measuring linkage: The software controls the turret, loading and directly reading the Vickers hardness value.
- •Light source linkage: Automatic focus.
- •Image acquisition: Real time display of hardness image, store and print image.
- •Automatic measurement: Automatically find the four vertices of indentation with fast speed and accurate data, there are many professional algorithms to be suitable for different indentation. It continuously and immediately measures at specified coordinates once loading.
- •Automatic point search: The system automatically finds the best vertices near the four vertices of the indentation, greatly reduce the human error.
- Diagonal measurement: Click the top left and lower right corner of the indentation, you can read the hardness value.
- Four point measurement: Click the four point of the indentation and you can read the hardness value.
- Hardness conversion: According to the national standard, automatically convert the hardness value between Brinell, Rockwell, Vickers, Knoop, real-time display.
- Graphic report: Automatic record of measurement data, automatic generation of hardness-depth curves, saving or printing the hardness-depth curves and all indentation measurements. Save or print the indentation image and the current indentation hardness value. All the reports are saved in WORD file.
- Results statistics: Output the multiple measured results of indentations by EXCEL and automatically count the measurement number, maximum value, minimum value, average value, variance, etc. of hardness.
- •Linkage control: Through the communication interface the system percepts the test force changes, controls the turret, loads and directly reads.
- •Automatic displacement: Equipped with high precision X-Y automatic test table.
- Automatic identification: Leading indentation automatic identification technology, read D1 / D2 and HV value in 0.3 seconds.
- •Stable performance: The indentation of non mirror polishing, uneven light, not in the center can be read automatically.
- Powerful functions: Such as manual reading, automatic reading, hardness conversion, depth-hardness curve, indentation image, picture and text report.
- Easy to use: Through the hardness block calibration, in line with the users' habits. It can be normal used with half day training.
- Automatic reading: Original algorithm of automatic reading to automatic read a variety of indentation with fast speed and high accuracy.
- •Good repeatability: It is automatic reading with high repeatability and can satisfy the requirement of professional users.

Automatic scanning: Can automatically scan the sample edge and shape.

Standard Delivery

●Computer (Hard disk: 500G,		●Control Cables	1
Memory: 4G, 19 inch LCD screen)	1	●RS232 Cable	1
●Ink Jet Printer	1	Joystick	1
●CCD Camera	1	 Motorized Test Table 	1
●1.5× Adapter	1	 Motorized Test Table Control Box 	1
●USB Softdog	1	Measuring Software	1